


NO.	DRAWING NO.	DESCRIPTION	QTY
1	P5-AR06-01-00-P-RP4	Wooden Backrest	1
2	P5-AR07-01-00-P-R4	Front wooden plate	2
3	P3-AR04-02-00-A-R3	Backrest Mechanism	2
4	P5-AR06-02-00-P-RP0	Backrest cushion	1
5	P5-AR06-03-00-P-RP2	Long Cushion	1
6	P5-AR07-02-00-P-RP1	Short Cushion	3
7	P3-AR04-01-00-P-R1	Stem	1
8	P3-AR04-03-02-P-R1	Front Tube Sleeve	1
9	P5-AR11-01-02-P-R0	Front Tube M	1
10	P3-AR04-06-00-P-R0	Tube Clamp Serration	2
11	P5-AR11-01-00-P-R0	Rear Tube	1
12	P3-AR04-04-00-P-R3	Rear tube sleeve	2
13		Quick Release	1
14		O-Ring 25 x 2.65	2
15		M4x25 Screw DIN912	4
16		M5x35 Screw ISO14583	14
17		M6x35 Screw DIN912	1
18		M5 Washer DIN9021	28
19		M6 Washer DIN125	2
20		M4 Nut DIN985	4
21		M5 Nut DIN985	14
22		M6 Nut DIN985	1



NO.	DRAWING NO.	DESCRIPTION	QTY
1	P5-AR06-01-00-P-RP4	Wooden Backrest	1
2	P5-AR07-01-00-P-R4	Front wooden plate	1
3	P3-AR04-02-00-A-R3	Backrest Mechanism	2
4	P5-AR06-02-00-P-RP0	Backrest cushion	1
5	P5-AR06-03-00-P-RP2	Long Cushion	1
6	P5-AR07-02-00-P-RP1	Short Cushion	2
7	P3-AR04-01-00-P-R1	Stem	1
8	P3-AR04-03-02-P-R1	Front Tube Sleeve	1
9	P5-AR11-01-02-P-R0	Front Tube M	1
10	P3-AR04-06-00-P-R0	Tube Clamp Serration	2
11	P5-AR11-01-00-P-R0	Rear Tube	1
12	P3-AR04-04-00-P-R3	Rear tube sleeve	2
13		Quick Release	1
14		O-Ring 25 x 2.65	2
15		M4x25 Screw DIN912	4
16		M5x35 Screw ISO14583	10
17		M6x35 Screw DIN912	1
18		M5 Washer DIN9021	20
19		M6 Washer DIN125	2
20		M4 Nut DIN985	4
21		M5 Nut DIN985	10
22		M6 Nut DIN985	1